







| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.06.24 | 阿树     |



| Led Color | Part No      | VR   | IF   | Recommended Operating | IF   |      |
|-----------|--------------|------|------|-----------------------|------|------|
|           |              |      |      |                       | Nom  | Max  |
| White     | TM-001-D6-01 | DC5V | 20mA | 20mA                  | 3.0V | 3.6V |
| Red       | TM-001-D6-02 | DC5V | 20mA | 20mA                  | 1.7V | 2.4V |
| Blue      | TM-001-D6-03 | DC5V | 20mA | 20mA                  | 3.0V | 3.6V |
| Green     | TM-001-D6-04 | DC5V | 20mA | 20mA                  | 1.9V | 2.4V |
| Yellow    | TM-001-D6-05 | DC5V | 20mA | 20mA                  | 1.9V | 2.4V |

| 7    | LED       | 1   |               |           |
|------|-----------|-----|---------------|-----------|
| 6    | Hat       | 1   | ABS           | Ag Plated |
| 5    | Terminal  | 4   | Brass (0.30t) |           |
| 4    | Contact   | 1   | F.ag/SUS      |           |
| 3    | Base      | 1   | PA66          |           |
| 2    | Cover     | 1   | PA66          |           |
| 1    | Keystake  | 1   | PA66          |           |
| ITEM | PAPT NAMF | QTY | MATERIAL      | FINISHING |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERAUCES |       |



|          |    |             |                         |
|----------|----|-------------|-------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE: LED SWITCH  |
| CHECKED  |    | UNIT: mm/in | PART NO.: TM-001-D6-05  |
| APPROVED |    | SIZE: A4    | DWG NO.: X-TM-001-D6-05 |