


Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:23A AC/DC

额定电流: 23A AC/DC

Withstanding voltage:2200V AC/minute

耐受电压: 2200V AC/分钟

Temperature range:-40℃~+105℃



温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤2mΩ

接触电阻: ≤2mΩ




X5700 H - 2x03 - N0
① ② ③ ④

1.Series No


2.Category:H-HSG

3.Row No.Pin No:2xXX-2x01~2x06P


4.Material:N0-PA66 94V-0 Black




2x01P




2x02P




2x03P



2x04P



2x05P



2x06P

Poles	Dimensions(mm)
	A
2x01	8.35
2x02	12.05
2x03	17.75
2x04	23.45
2x05	29.15
2x06	34.85

X5700H-2x03-N0	PA66	X5700W	X5700T
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	5.7mm Crimp Style Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X5700H-2x03-N0
		DWG NO.:
		X-X5700H-2x03-N0
WEIGHT	SHEET	REVISION
	1/1	A0