







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.31	阿 树





Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-45℃-+125℃
温度范围: -45℃-+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

PART NO.:
X9357 W R-03-46 SN
① ② ③ ④ ⑤ ⑥

- ① Series No
- ② Category:W-Wager
- ③ Welding Board Angle:R-Straight 90°
- ④ Row No.Pin No:XX-02~06 P
- ⑤ Material:46-PA46 UL94V-0
- ⑥ Plating:SN-Plated Tin



3 Pin



2,4,5,6 Pin

Poles	Dimensions(mm)	
	A	B
02	4.20	9.60
03	8.40	13.80
04	12.60	18.00
05	16.80	22.20
06	21.00	26.40

X9357WR-03-46SN		PA46	Brass	X9357HM	
PART NO		Material	Material(Pin)	Suitable XKB Housing	
DESIGN	阿 树	VIEW: 	MODEL TYPE: 4.20 mm Crimp Style Connectors		
CHECKED		UNIT: mm/in	PART NO.: X9357WR-03-46SN		
APPROVED		SIZE: A4	DWG NO.: X-X9357WR-03-46SN		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED