



PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage: 300V AC/minute
 耐受电压: 300V AC/分钟
 Temperature range: -40℃~+105℃
 温度范围: -40℃~+105℃
 Insulation resistance: ≥500MΩ
 绝缘电阻: ≥500MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 Material: PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category: 1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature: 255±5℃, 10S
 波峰焊温度: 255±5℃, 10S

X1311 F V - 06 - C43 D24
 ① ② ③ ④ ⑤ ⑥

1. Series No
2. Category: F-Female
3. Welding Board Angle: V-Straight 180°
4. Row No. Pin No: XX-02~40 Pin
5. Plastic height: C=4.3mm
6. Pin Length: D=2.4mm

X1311FV-06-C43D24	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1311FV-06-C43D24
APPD	SIZE: A4	DWG NO.: X-X1311FV-06-C43D24
		WEIGHT
		SHEET 1/1
		REVISION A0