






POLARIZATION SLOT LOCATION



02 Pin



03 Pin



SECTION:A-A

Specifications:

规格:

Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X9556 H F - 04 - PT
① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-HSG
- 3.Category:F-Female Housing
- 4.Row No.Pin No:XX-02~20P
- 5.Material:PT-PBT UL94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.54	7.12	12	27.94	32.52
03	5.08	9.66	13	30.48	35.06
04	7.62	12.20	14	33.02	37.60
05	10.16	14.74	15	35.56	40.14
06	12.70	17.28	16	38.10	42.68
07	15.24	19.82	17	40.64	45.22
08	17.78	22.36	18	43.18	47.76
09	20.32	24.90	19	45.72	50.30
10	22.86	27.44	20	48.26	52.84
11	25.40	29.98	/		

X9556HF-04-PT	PBT	X9556H	X9556TM
PART N0	Material	Suitable XKB Housing	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector
DWN		VIEW:	PART NO.: X9556HF-04-PT
CHKD		UNIT: mm/in	DWG NO.: X-X9556HF-04-PT
APPD		SIZE: A4	

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT SHEET REVISION
1/1 A0