





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.27	阿树



规格 Specifications:
额定电压 Voltage rating:250VAC/DC.
额定电流 Current rating:1A AC/DC
耐电压 Withstanding voltage:300V AC/minute
温度区间 Temperature range:-40℃to+105℃
绝缘电阻 Insulation resistance:≥500MΩ Min
接触电阻 Contact resistance:≤20MΩ Max
材料 Material: PA6T 94V-0
镀层 Plating Category: 1U"Gold
波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:
X1311 W V-16 J-C18 D27
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Water
- ③Welding Board Angle:V-Straight 180°
- ④Row No -Pin No:XX-01P-40P
- ⑤Plastic height: J=1.0mm
- ⑥Plastic length:C=2.7mm
- ⑦Plastic length:D=1.8mm

X1311WV-16J-C18D27	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.27mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X1311WV-16J-C18D27
APPROVED		SIZE: A4	DWG NO.: X-X1311WV-16J-C18D27
SCALE			PAGE
N/A			1/1
REVISION			A1