







REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/
A1	N/A		图面升级整理图面	2025.06.23




Circuit diagram

DMX-XXXN-X
1:1A以下
3:3A

7	Lever	1	SUS	Nature
6	Contact Point	1	Silver	Nature
5	Spring Plate	1	BeCu	Nature
4	Terminal	3	Barss strip	Ag Plated
3	Base	1	PBT	White
2	Cover	1	PBT	Black
1	Button	1	PBT	White
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

1:转换型 SPDT		2:常闭型 SPST-NC		3:常开型 SPST-NO	
					
COM NO NC		COM NC		COM NO	
AuGLAR	±5°				
X.	±0.40				
X.x	±0.30				
X.xx	±0.20				
X.xxx	±0.15				
UNSPECIFIED TOLERAUCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			



DESIGN	阿树	VIEW:		MODEL TYPE:	MICRO SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	DM1-135N-1
APPROVED		SIZE:	A4	DWG NO.:	X-DM1-135N-1
		SCALE	N/A	PAGE	1/1
		REVISION	A1		