







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.8	阿树




Temperature range: -40℃ - +125℃
温度范围: -40℃ - +125℃



PART NO.:
K 776280 H-08-PT W
① ② ③ ④ ⑤ ⑥

- ①K:XKBTEK—Car Connector
②XKB Series No
③Category:H—Housing
④Row No.Pin No:08 Pin
⑤Material:PT—PBT
⑥Color:X:B—Black; W—White;



Slot location	Color	PART NO
2 4	Black	K776280H-08-PTB
1 3	White	K776280H-08-PTW

5	Terminal locks	Red	PBT	1
4	Rubber rings	Yellow	Silica gel	1
3	Housing		PBT	1
2	Rubber plugs	Yellow	Silica gel	1
1	Cover	Black	PBT	1
NO	NAME	COLOR	MATERIAL	QTY

K776280H-08-PTW	PBT	K776280W	K776280T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	4.0mm Automobile connector
CHECKED		UNIT:	mm/in	PART NO.:	K776280H-08-PTW
APPROVED		SIZE:	A4	DWG NO.:	X-K776280H-08-PTW