



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 7A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\ \Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X9396 W R -09 A- N0 SN

① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category : W-WAFER

③ Wedding Board Angle : R-Stright 90°

④ Row No.Pin No.XX-02-15

⑤ Special No.A-There are graps

⑥ Material:46-PA46 94V-0

⑦ Planting Category: SN-Bright tin plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.96	7.92	09	31.68	35.64
03	7.92	11.88	10	35.64	39.60
04	11.88	15.84	11	39.60	43.56
05	15.84	19.80	12	43.56	47.52
06	19.80	23.76	13	47.52	51.48
07	23.76	27.72	14	51.48	55.44
08	27.72	31.68	15	55.44	59.40

X9396WR-09A-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9396H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable X K B Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connectors			
Δx					ANGULAR	$\pm 5^{\circ}$	DWN		DATE		VIEW: 	PART NO.: X9396WR-09A-N0SN			
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9396WR-09A-N0SN			
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4				
Δx					$16 < L \leq 63$	± 0.4									
MARK	DESCRIPTION				DATE	REVISED	APPROVED								
REVISIONS															
							UNSPECIFIED TOLERANCES								
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0	