







PCB LAYOUT

接触电阻: 20mΩ Max

X2015 W V - 2x07 - 46 SN
 (1) (2) (3) (4) (5) (6)

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Row No.Pin No:2xXX-2x02~2x20P
5.Material:46-Nylon46 UL94V-0
6.Plating:SN-Tin Plated

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x02	2.00	6.00	2x08	14.00	18.00
2x03	4.00	8.00	2x09	16.00	20.00
2x04	6.00	10.00	2x10	18.00	22.00
2x05	8.00	12.00	2x11	20.00	24.00
2x06	10.00	14.00	2x12	22.00	26.00
2x07	12.00	16.00	2x20	38.00	42.00

X2015WV-2x07-46SN	Nylon46	Brass	X2015H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X2015WV-2x07-46SN
CHKD		UNIT: mm/in	DWG NO.: X-X2015WV-2x07-46SN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED