




Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min


Contact resistance:20mΩ Max

接触电阻: 20mΩ Max


X9357 W R- 2x05 B -N0 SN

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board angle:R-Stright 90°
- 4.Row No.Pin No:2xXX-2x01P-2x12P
- 5.Specal No:B-A rrange ushering with positioning column
- 6.Material:N0-PA66 UL 94V-0
- 7.Plating:SN-Tin plated or Gold Flash



PCB LAYOUT :Component Side
Recommended PCB Thickness 1.78MAX



CIRCUIT SIZE LAYOUT

Poles	Dimensions(mm)	
	A	B
2x01	/	10.80
2x02	4.20	15.00
2x03	8.40	19.20
2x04	12.60	23.40
2x05	16.80	27.60
2x06	21.00	31.00
2x07	25.20	36.00
2x08	29.40	40.20
2x09	33.60	44.40
2x10	37.80	48.60
2x11	42.00	52.80
2x12	46.20	57.00

X9357WR-2x05B-N0SN	PA66	Brass	X9357HM-B
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

DSND	SCALE: N/A	MODEL TYPE: 4.2mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X9357WR-2x05B-N0SN	
CHKD	UNIT: mm/in	DWG NO.: X-X9357WR-2x05B-N0SN	
APPD	SIZE: A4	WEIGHT	SHEET 1/1
XKB INDUSTRIAL PRECISION CO.,LIMITED		REVISION A0	