











RECOMMENDED P.C.B LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$


NOTES:

SPECIFICATION:

- 1.CURRENT RATING: 3.0A MAX
- 2.VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: $-30^{\circ}\text{C}\sim 85^{\circ}\text{C}$
- 4.CONTACT RESISTANCE: 40 MILLIONHM MAX
- 5.INSULATION RESISTANCE: 100 MEGOHMS MIN
- 6.LNSERTION FORCE: 5N~20N
- 7.UNMATING FORCE: 8N~20N
- 8.DURABILITY: 10.000 CYCLES
- 9.WATER PROOFNESS: THIS PRODUCT IS BASED ON IPX7



加防水圈示意图



U262-061N-4BF711

1:0.8u"
2:5u"
3:10u"

W:WHITE
B:BLACK
1:PBT
2:PA6T
3:PA9T
4:LCP

PIN ASSIGNMENT:

PIN NO	A1&B12	A4&B9	A5	A5	A9&B4	A12&B1
SIGNAL NAME	GND	VBUS	CC1	CC2	VBUS	GND
PCB PAD NO.	C1	C2	C3	C4	C5	C6

5	SHELL	STAINLESS STEEL	Ni Plated	1PCS
4	SHIELDING PLATE	STAINLESS STEEL	Ni Plated	1PCS
3	CONTACT	COPPER ALLOY	TIN/Au/Ni Plated	1SET
2	SHELL HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

					ANGULAR	$\pm 5^{\circ}$
Δx					$L \leq 4$	± 0.2
Δx					$4 < L \leq 16$	± 0.3
Δx					$16 < L \leq 63$	± 0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5
REVISIONS						
UNSPECIFIED TOLERANCES						
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

DSND		SCALE: N/A	MODEL TYPE: Type-C 3.1
DWN		VIEW:	PART NO.: U262-061N-4BF711
CHKD		UNIT: mm/in	DWG NO.: X-U262-061N-4BF711
APPD		SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1/1 A0