




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品尺寸变更, 图面升级整理图面	2024.08.30	阿树



电器功能 Function		
ON	NA	ON
	/	

Specification.
1.Rating:6A 120VAC
2.Contact resistance: ≤ 30 mQ
3.Insulation resistance: >100 MQ(DC500V/Min)
4.Electronics life: >10000 cycles
5.Operation force:250+100gf



SS-12M11	G	4
Knob Type	H(MM)	
L	2 ~ 12	
G		

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH	
CHECKED		UNIT:	mm/in	PART NO.:	SS-12M11G4	
APPROVED		SIZE:	A4	DWG NO.:	X-SS-12M11G4	
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1