





Recommended PCB Layout(Top view)
Tolerance:±0.05mm

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

<u>X2026</u>	<u>W</u>	<u>V - 2x10</u>	<u>D</u>	<u>R - LP</u>	<u>SN</u>		
①	②	③	④	⑤	⑥	⑦	⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Row No.Pin No:2xXX-2x02~2x16Pin

5.Special No:D-With Lock

6.Special No:R-DIP 2.0mm

7.Material:LP-LCP UL94V-0 ,Natural

CAP:LCP UL94V-0 ,Natural

8.Plating:SN- Tin Plated

Poles	Dimensions (mm)					Poles	Dimensions (mm)				
	A	B	C	D	E		A	B	C	D	E
2x02	2.00	4.95	6.60		4.50	2x10	18.00	20.95	22.60	15.00	6.50
2x03	4.00	6.95	8.60	3.00		2x11	20.00	22.95	24.60	17.00	
2x04	6.00	8.95	10.60			2x12	22.00	24.95	26.60	19.00	
2x05	8.00	10.95	12.60	5.00		2x13	24.00	26.95	28.60	21.00	
2x06	10.00	12.95	14.60	7.00	6.50	2x14	26.00	28.95	30.60	23.00	
2x07	12.00	14.95	16.60	9.00		2x15	28.00	30.95	32.60	25.00	
2x08	14.00	16.95	18.60	11.00		2x16	30.00	32.95	34.60	27.00	
2x09	16.00	18.95	20.60	13.00		/					

X2026WV-2x10DR-LPSN	LCP	Brass	X2026H
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X2026WV-2x10DR-LPSN		
CHKD		UNIT: mm/in	DWG NO.: X-X2026WV-2x10DR-LPSN		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0