




#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

#### X2026 H -2x10B-N0

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:H-HSG

3.Appearance type:Blank-Ordinary

4.Row No-Pin No:2xXX-2x02P~2x22P

5.Plug the Pin&Special N0:

B-With Lock In the middle

6.Material:N0-PA66 94V-0

7.Color:Blank-Natural Color;BK-Black

| poles | Dimensions(mm) |       |       | poles | Dimensions(mm) |       |       | Poles | Dimensions(mm) |       |       |
|-------|----------------|-------|-------|-------|----------------|-------|-------|-------|----------------|-------|-------|
|       | A              | B     | C     |       | A              | B     | C     |       | A              | B     | C     |
| 2x02  | 2.00           | 5.90  | 4.60  | 2x10  | 18.00          | 21.90 | 20.60 | 2x18  | 34.00          | 37.90 | 36.60 |
| 2x03  | 4.00           | 7.90  | 6.60  | 2x11  | 20.00          | 23.90 | 22.60 | 2x19  | 36.00          | 39.90 | 38.60 |
| 2x04  | 6.00           | 9.90  | 8.60  | 2x12  | 22.00          | 25.90 | 24.60 | 2x20  | 38.00          | 41.90 | 40.60 |
| 2x05  | 8.00           | 11.90 | 10.60 | 2x13  | 24.00          | 27.90 | 26.60 | 2x21  | 40.00          | 43.90 | 42.60 |
| 2x06  | 10.00          | 13.90 | 12.60 | 2x14  | 26.00          | 29.90 | 28.60 | 2x22  | 42.00          | 45.90 | 44.60 |
| 2x07  | 12.00          | 15.90 | 14.60 | 2x15  | 28.00          | 31.90 | 30.60 |       |                |       |       |
| 2x08  | 14.00          | 17.90 | 16.60 | 2x16  | 30.00          | 33.90 | 32.60 |       |                |       |       |
| 2x09  | 16.00          | 19.90 | 18.60 | 2x17  | 32.00          | 35.90 | 34.60 |       |                |       |       |

|                   |                          |                       |                    |
|-------------------|--------------------------|-----------------------|--------------------|
| X2026H-2x10B-N0BK | Nylon 66 UL 94V-0(Black) | X2026T-B              | X2026W-B           |
| X2026H-2x10B-N0   | Nylon 66 UL 94V-0        |                       |                    |
| PART NO           | Material                 | Suitable XKB Terminal | Suitable XKB Wafer |

Wire to board connector

|                                                     |             |  |  |      |            |          |                                      |  |      |  |                                                                                             |                                              |              |                |  |
|-----------------------------------------------------|-------------|--|--|------|------------|----------|--------------------------------------|--|------|--|---------------------------------------------------------------------------------------------|----------------------------------------------|--------------|----------------|--|
|                                                     |             |  |  |      |            |          | DSND                                 |  | DATE |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.00mm Crimp Style Connectors |              |                |  |
|                                                     |             |  |  |      | units:     | mm       | DWN                                  |  | DATE |  | VIEW:  | PART NO.:<br>X2026H-2x10B-N0                 |              |                |  |
| Δx                                                  |             |  |  |      | tolerance: |          | CHKD                                 |  | DATE |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2026H-2x10B-N0                |              |                |  |
| Δx                                                  |             |  |  |      | X.X        | ±0.2mm   | APPD                                 |  | DATE |  | SIZE: A4                                                                                    | WEIGHT<br>1.0g                               | SHEET<br>1/1 | REVISION<br>A0 |  |
| Δx                                                  |             |  |  |      | X.XX       | ±0.1mm   |                                      |  |      |  |                                                                                             |                                              |              |                |  |
| Δx                                                  |             |  |  |      | X.XXX      | ±0.05mm  |                                      |  |      |  |                                                                                             |                                              |              |                |  |
| MARK                                                | DESCRIPTION |  |  | DATE | REVISED    | APPROVED |                                      |  |      |  |                                                                                             |                                              |              |                |  |
| REVISIONS                                           |             |  |  |      |            |          |                                      |  |      |  |                                                                                             |                                              |              |                |  |
| UNSPECIFIED TOLERANCES                              |             |  |  |      |            |          |                                      |  |      |  |                                                                                             |                                              |              |                |  |
| www.xk-dg.cn    www.helloxkb.com    www.helloxkb.cn |             |  |  |      |            |          | XKB INDUSTRIAL PRECISION CO.,LIMITED |  |      |  |                                                                                             |                                              |              |                |  |