


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.01.07	阿树



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

PART NO.:

K 174051 T-B SN-D
① ② ③ ④ ⑤ ⑥

- ①K:XKBTEK-Car Connector
②XKB Series No
③Category:T-Terminal
④Material:B-Brass
⑤Plating:SN-Plating Tin
⑥Special No:D-Glass D Termianl

K174051T-BSN-D	Brass	AWG#20-22	K174051H
PART NO	Material	Wire Range	Suitable XKB Housing
DESIGN	阿树	VIEW:	MODEL TYPE: 2.5mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: K174051T-BSN-D
APPROVED		SIZE: A4	DWG NO.:
SCALE			PAGE
N/A			1/1
REVISION			A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED