




PCB LAYOUT



Specifications:

规格:
Voltage rating: 250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage: 1000V AC/minute
耐受电压: 1000V AC/分钟
Temperature range: -40°C~+105°C
温度范围: -40°C~+105°C
Insulation resistance: ≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
Material: PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category: 1U"Gold
镀层: 1U"Gold
Wave soldering temperature: 255±5°C, 10S
波峰焊温度: 255±5°C, 10S

X6521 F V - 2x03 - C85 D32
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:2xXX-2x01~2x40P
- 5.Plastic Height:C=8.5mm
- 6.Pin Length:D=3.2mm

X6521FV-2x03-C85D32	PA6T	Brass	X6521W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR
ΔX					L ≤ 4
ΔX					4 < L ≤ 16
ΔX					16 < L ≤ 63
MARK					L > 63

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X6521FV-2x03-C85D32
APPD	SIZE: A4	DWG NO.: X-X6521FV-2x03-C85D32
		WEIGHT
		SHEET
		REVISION
		1/1
		A0