

1

2

3

4

A

B

C


D

A

B

C


D



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.30	阿树

Rated electrical load: DC30v/0.5A
额定电气负载: DC30v/0.5A
Contact resistance: $\leq 0.03 \Omega$
接触电阻: $\leq 0.03 \Omega$
Insulation resistance: $\geq 100m \Omega$
绝缘电阻: $\geq 100m \Omega$
Withstand voltage: AC500V (50 Hz) / min
耐受电压: AC500V (50Hz) / min
Insertion and extraction force: 3-20N
插拔力: 3-20N
Service temperature range: $-30-70^{\circ}C$
工作温度范围: $-30-70^{\circ}C$
Service life: 5000 times
使用寿命: 5000次

Model No.	PJ-43502PM
Schematic	 2 5 6 3 4 7



plastic 1	PC	
Terminal 7	Phosphorous copper	Gold
Terminal 6	Phosphorous copper	Gold
Terminal 5	Phosphorous copper	Gold
Terminal 4	Phosphorous copper	Gold
Terminal 3	Phosphorous copper	Gold
Terminal 2	Phosphorous copper	Gold
Terminal 1	Phosphorous copper	Gold
PAPT NAMF	MATERIAL	PLATING

AuGLAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	3.5 PHONE JACK
CHECKED		UNIT:	mm/in	PART NO.:	PJ-H395
APPROVED		SIZE:	A4	DWG NO.:	X-PJ-H395

1

2

3

4