





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.09.13	阿树



Specifications:

规格:

Voltage rating:34V AC/DC

额定电压: 34V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance:≥100MΩ min

绝缘电阻: ≥100MΩ Min

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

PART NO.:

X2500 F R-22 S-46 SN
① ② ③ ④ ⑤ ⑥ ⑦

①Series No

②Category:F-Female

③Welding Board Angle:R-Stright 90°

④No.of Pins: XX-22 PIN

⑤Special No:S-Positioning post with harpoon

⑥Material:46-PA46 94V-0

⑦Plating :AuSn-Terminal half-AuSn

X2500FR-22S-46SN	PA46	Phosphor Bronze	X2500W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.5mm BTB Connecto
CHECKED		UNIT:	mm/in	PART NO.:	X2500FR-22S-46SN
APPROVED		SIZE:	A4	DWG NO.:	X-X2500FR-22S-46SN