








2x01P




2x02P




2x03P



2x04P



2x05P



2x06P

Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:23A AC/DC

额定电流: 23A AC/DC

Withstanding voltage:2200V AC/minute

耐受电压: 2200V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤2mΩ

接触电阻: ≤2mΩ

X5700 H - 2x06 - N0
① ② ③ ④

1.Series No

2.Category:H-HSG

3.Row No.Pin No:2xXX-2x01~2x06P

4.Material:N0-PA66 94V-0 Black

Poles	Dimensions(mm)
	A
2x01	8.35
2x02	12.05
2x03	17.75
2x04	23.45
2x05	29.15
2x06	34.85

X5700H-2x06-N0	PA66	X5700W	X5700T
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
MARK					
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 5.7mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X5700H-2x06-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X5700H-2x06-N0		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0