

Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:23A AC/DC

额定电流: 23A AC/DC

Withstanding voltage:2200V AC/minute

耐受电压: 2200V AC/分钟

Temperature range:-40°C-+105°C


温度范围: -40℃-+105℃

Insulation resistance: $\geq 1000\text{M}\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 2\text{m}\Omega$

接触电阻: $\leq 2\text{m}\Omega$



$$\frac{X5700}{\textcircled{1}} \quad \frac{H}{\textcircled{2}} - \frac{2x05}{\textcircled{3}} - \frac{N0}{\textcircled{4}}$$

1.Series No

2. Category: H-HSG

3.Row No.Pin No:2xXX-2x01~2x06P

4.Material:N0-PA66 94V-0 Black



2x01P

2x02P

2x03P

2x04P

2x05P

2x06P

Poles	Dimensions(mm)
	A
2x01	8.35
2x02	12.05
2x03	17.75
2x04	23.45
2x05	29.15
2x06	34.85

X5700H-2x05-N0	PA66	X5700W	X5700T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

REVISIONS

UNSPECIFIED TOLERANCES

XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 5.7mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X5700H-2x05-N0
CHKD		UNIT: mm/in	DWG NO.: X-X5700H-2x05-N0
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0