




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树






Circuit diagram

DM1-117N-1

1:1A以下
3:3A

7	Lever	1	SUS	Nature
6	Contact Point	1	Silver	Nature
5	Spring Plate	1	BeCu	Nature
4	Terminal	3	Barss strip	Ag Plated
3	Base	1	PBT	White
2	Cover	1	PBT	Black
1	Button	1	PBT	White
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

1:转换型 SPDT		2:常闭型 SPST-NC		3:常开型 SPST-NO	
					
AuGLAR		±5°		 <i>Connection</i>	
X.		±0.40			
X.x		±0.30			
X.xx		±0.20			
X.xxx		±0.15			
UNSPECIFIED TOLERAUCES					

DESIGN	阿树	VIEW:		MODEL TYPE:	MICRO SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	DM1-117N-1
APPROVED		SIZE:	A4	DWG NO.:	

 117	 135
 150	 180
 12U	 16U
 115G	 151U
 141U	 000