





- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 20\text{m}\Omega$
- After environmental testing : $\leq 30\text{m}\Omega$

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: XX-02P~16P
- ⑤ Material : N0-PA66 94V-0
- ⑥ Plating Category : Sn-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	5.20	10	18.00	22.00	21
03	4.00	8.00	7.20	11	20.00	24.00	23
04	6.00	10.00	9.20	12	22.00	26.00	25
05	8.00	12.00	11.20	13	24.00	28.00	27
06	10.0	14.00	13.20	14	26.00	30.00	29
07	12.0	16.00	15.20	15	28.00	32.00	31
08	14.0	18.00	17.20				
09	16.0	20.00	19.20				

X2012WV-13-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2012H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
ΔX					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X2012WV-13-N0SN		
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2012WV-13-N0SN		
ΔX					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4			
ΔX					$16 < L \leq 63$	± 0.4								
MARK	DESCRIPTION				DATE	REVISED	APPROVED							
REVISIONS							UNSPECIFIED TOLERANCES							
www.xk-da.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0