

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树

SPECIFICATION
Contact Rating: 50mA, 12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min. 500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.20mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃

PAPT NO	TS-1187M-C
Operating Force	A:100gf B:160gf C:260gf
Height	H:0.8

⑤	Terminal	4	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	Lcp		
②	Cover	1	Brass	Plating Nickel	
①	Keystake	1			
ITEM	PAPT	NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCE	

DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
TACT SWITCH
PART NO.:
TS-1187M-C
DWG NO.:
TS-1187M-C

SCALE	PAGE	REVISION
N/A	1/1	A1

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

XKB INDUSTRIAL PRECISION CO.,LIMITED