

1


2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.4	阿树

A






PART NO.:

K 137635 H M-2x18 B-N0
① ② ③ ④ ⑤ ⑥ ⑦


- ①K:XKBTEK-Car Connector
- ②XKB Series No
- ③Category:H-Housing
- ④Category:M-Male Housing
- ⑤Row No.Pin No:2x18 Pin
- ⑥Special No:B-Misaligned foot
- ⑦Material:N0-PA66 UL 94V-0

Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃--+125℃
温度范围: -40℃--+125℃

B



C



D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	2.2mm Automobile connector
PART NO.:	K137635HM-2x18B-N0
DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1

1

2

3

4