


#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001 H3 -2x12 PT V01  
① ② ③ ④ ⑤

1.Series No

2.Category:H3-Two piece with bow button

3.Row No.Pin No:2xXX-2x03P-2x30P

4.Material:PT-PBT Glass Fiber UL94V-0

5.Plating:V01-Gold Flash

| Poles | DIM A | DIM B |
|-------|-------|-------|
| 2x03  | 11.20 | 4.00  |
| 2x04  | 13.20 | 6.00  |
| 2x05  | 15.20 | 8.00  |
| 2x06  | 17.20 | 10.00 |
| 2x07  | 19.20 | 12.00 |
| 2x08  | 21.20 | 14.00 |
| 2x09  | 23.20 | 16.00 |
| 2x10  | 25.20 | 18.00 |
| 2x11  | 27.20 | 20.00 |
| 2x12  | 29.20 | 22.00 |
| 2x13  | 31.20 | 24.00 |
| 2x14  | 33.20 | 26.00 |
| 2x15  | 35.20 | 28.00 |
| 2x17  | 39.20 | 32.00 |
| 2x18  | 41.20 | 34.00 |
| 2x20  | 45.20 | 38.00 |
| 2x22  | 49.20 | 42.00 |
| 2x25  | 55.20 | 48.00 |
| 2x30  | 65.20 | 58.00 |

|                    |                 |               |                    |
|--------------------|-----------------|---------------|--------------------|
| X2001H3-2x12-PTV01 | PBT Glass Fiber | Brass         | X2001W-B           |
| PART NO            | Material        | Material(Pin) | Suitable XKB Wafer |

|                                               |  |  |  |  |                        |      |
|-----------------------------------------------|--|--|--|--|------------------------|------|
|                                               |  |  |  |  | ANGLAR                 | ±5°  |
| ΔX                                            |  |  |  |  | L≤ 4                   | ±0.2 |
| ΔX                                            |  |  |  |  | 4<L≤ 16                | ±0.3 |
| ΔX                                            |  |  |  |  | 16<L≤ 63               | ±0.4 |
| MARK                                          |  |  |  |  | L> 63                  | ±0.5 |
| REVISIONS                                     |  |  |  |  | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |                        |      |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|      |  |             |                      |
|------|--|-------------|----------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:          |
| DWN  |  | VIEW:       | 2.0mm IDC Connector  |
| CHKD |  | UNIT: mm/in | PART NO.:            |
| APPD |  | SIZE: A4    | X2001H3-2x12-PTV01   |
|      |  |             | DWG NO.:             |
|      |  |             | X-X2001H3-2x12-PTV01 |
|      |  | WEIGHT      | SHEET                |
|      |  |             | 1/1                  |
|      |  | REVISION    | A0                   |