


端子: Phosphor Bronze

① ② ③ ④ ⑤ ⑥ ⑦

⑦See the Table of next page


$$A = 2.5 \times (\text{No. of circuit} - 1)$$
$$B = A + 5.0$$

X2514HI-02L-0-0A	PA66 94V-0	AWG #22-#24 AWG #26	Phosphor Bronze	X2514W
PART NO	Material	Wire Range	Material (Terminal)	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5 mm IDC Style Connectors			
Δx					ANGLAR	$\pm 5^{\circ}$	DWN		DATE		VIEW: 	PART NO.: X2514HI-02L-0-0A			
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2514HI-02L-0-0A			
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4				
Δx					$16 < L \leq 63$	± 0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED								
MARK	DESCRIPTION				DATE	REVISED							APPROVED	$L > 63$	± 0.5
REVISIONS													UNSPECIFIED TOLERANCES		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							WEIGHT 1.0g						SHEET 1/1	REVISION A0	