


PCB LAYOUT



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40°C-+105°C

温度范围: -40℃-+105℃

Insulation resistance: $\geq 1000\text{M}\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻: $\leq 20\text{m}\Omega$

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldring temperature: $255 \pm 5^\circ\text{C}$, 10S

波峰焊温度: $255 \pm 5^{\circ}\text{C}$, 10S

X6511 F V - 34 - C85 D32
 (1) (2) (3) (4) (5) (6)

1.Series No.

2.Category:F-Female

3.Welding Board Angle:V-Stright 180°

4.Row No -Pin No:XX-02P-40P

5. Plastic height: $C=8.5\text{mm}$

6.Pin Length:D=3.2mm

X6511FV-34-C85D32	PA6T	Brass	1U"Gold	X6511W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector		
DWN		VIEW: 	PART NO.: X6511FV-34-C85D32		
CHKD		UNIT: mm/in	DWG NO.: X-X6511FV-34-C85D32		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						