








TYPE 1



Y型端子



14P-64P 双槽



6P 小鼻/无槽

TYPE C

6P 大鼻/无槽

TYPE A

8P 大鼻/无槽

TYPE A

6P 小鼻/单槽

TYPE B

8P 小鼻/单槽

TYPE B

10P-12P 单槽

Blank

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X9555 H2 -2x18- PT V01

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H2-three-piece with TYPE1 HSG

3.Row No-Pin No:2xXX-2x03P~2x32P

4.Special:NO:X Type A or Type B and Type C

Blank-conventional product

5.Material:PT-PBT UL94V-0

6.Plating:V01-Gold Flash

X9555H2-2x18-PTV01	PBT	BRASS	Gold Flash	X9555WV-2xXX	XPD1.27-A28PXX-IDC	X9555HI-2xXXA
				X9555WR-2xXX		X9555HI-2xXXB
X9555WVS-2xXX				X9555HI-2xXXC		
X9555WV-2xXX				X9555HI-2xXXA		
X9555WR-2xXX				X9555HI-2xXXB		
X9555H2-2x18-PTV01				X9555WVS-2xXX		X9555HI-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Wafer	Suitable XKB flat cable	Suitable XKB DIP

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
2x03	12.32	5.08	1.9	2x13	37.72	30.48	3.8
2x04	14.86	7.62	小1.9/大3.8	2x15	42.80	35.56	3.8
2x05	17.40	10.16	3.8	2x17	47.88	40.64	3.8
2x06	19.94	12.70	3.8	2x18	50.42	43.18	3.8
2x07	22.48	15.24	3.8	2x20	55.50	48.26	3.8
2x08	25.02	17.78	3.8	2x22	60.58	53.34	3.8
2x09	27.56	20.32	3.8	2x25	68.20	60.96	3.8
2x10	30.10	22.86	3.8	2x30	80.90	73.66	3.8
2x11	32.64	25.40	3.8	2x32	85.98	78.74	3.8
2x12	35.18	27.94	3.8				

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	
	DESCRIPTION	DATE	REVISED	APPROVED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm IDC		
DWN		VIEW:	PART NO.: X9555H2-2x18-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X9555H2-2x18-PTV01		
APPD		SIZE: A4			
			WEIGHT	SHEET 1/1	REVISION A0