







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.16	阿树



SK12D07L6B

L(mm)	Colour
2~12	B:Black
	R:Red



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(CYCLES)	10,000

4	Terminal	3	Brass(0.30t)	ag Plated
3	Base	1	Phenolic Resin	
2	Cover	1	Sus	Natural
1	Keystake	1	PA66	Black
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	SLIDE SWITCH
PART NO.:	SK12D07L6B
DWG NO.:	X-SK12D07L6B

SCALE	PAGE	REVISION
N/A	1/1	A1