




P.C.B LAYO UT

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω

X3025W V - 08C-LPSN

- ① Series No.
② Category :
W-wafer
③ Welding Board Angle:
V-180°
④ Welding Way:
Blank-DIP
⑤ Row No.-Pin No.
XX-Single row
⑥ Special NO.
C-With a harpoon
⑦ Material :
LP-LCP 94V-0 66-PA66 94V-0
⑧ Planting Category:
V**:All Gold-Plated
G**:Gold-Plated Contact
*01-Gold Flash ; *02-2u" ; *03-3u" ; *05-5u"
*10-10u" ; *15-15u" ; *30-30u" ; *50-50u"
SN-Bright tin plating 70u"
SN1-Bright tin plating 120u"Min. ;
SW-Fog Tin plating
⑨ Color :
Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
9	24.00	30.65
10	27.00	33.65
11	30.00	36.65
12	33.00	39.65

X3025WV-08C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WV-08C-LPSN	LCP UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
MARK					

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	3.00 mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	PART NO.: X3025WV-08C-XXSN
APPD		DATE		SIZE: A4	DWG NO.: X3025WV-08C-XXSN
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0