






Poles	Dimensions		Poles	Dimensions	
	A	B		A	B
2x03	21.92	4.00	2x13	41.92	24.00
2x04	23.92	6.00	2x15	45.92	28.00
2x05	25.92	8.00	2x17	49.92	32.00
2x06	27.92	10.00	2x18	51.92	34.00
2x07	29.92	12.00	2x20	55.92	38.00
2x08	31.92	14.00	2x22	59.92	42.00
2x10	35.92	18.00	2x25	65.92	48.00
2x12	39.92	22.00	2x30	75.92	58.00

$$B = 2.0 \cdot \frac{NP}{2} - 2.0 \pm 0.2$$

X2001WV-2x12C-6TV01	Nylon 6T	Brass	X2001HA2-2x12
PART NO	Material	Material(Pin)	Suitable XKB IDC

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Horn type connector		
DWN		VIEW: 	PART NO.: X2001WV-2x12C-6TV01		
CHKD		UNIT: mm/in	DWG NO.: X-X2001WV-2x12C-6TV01		
APPD		SIZE: A4			
L. PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0