







Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 1000V AC/ 分钟
Temperature range:-25 ℃ ~+85℃
温度范围: -25℃ ~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤30mΩ
接触电阻: ≤30mΩ
After environmental testing:≤40mΩ
环境测试后: ≤40兆欧

X2011 W V S-09 A- 9T SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:XX-02P~16P
- 6.Plug the Pin&Special No:A-With Located Block
- 7.Material:9T:PA9T UL 94V-0
- 8.Plating Category:SN-Bright Tin Plating
- 9.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2	2.00	8.00	10	18.00	24.00
3	4.00	10.00	11	20.00	26.00
4	6.00	12.00	12	22.00	28.00
5	8.00	14.00	13	24.00	30.00
6	10.00	16.00	14	26.00	32.00
7	12.00	18.00	15	28.00	34.00
8	14.00	20.00	16	30.00	36.00
9	16.00	22.00			

X2011WVS-09A-9TSN	PA9T UL 94V-0	Brass	Phosphor Bronze	Tin-Plated	X2011H-A
PART NO	Material	Material(pin)	Material(Solder Tab)	Finish(Pin and Solder tab)	Suitable XKB Housing

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors		
					units: mm	DWN		DATE		VIEW: 	PART NO.: X2011WVS-09A-9TSN		
Δ x					tolerance: X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2011WVS-09A-9TSN		
Δ x					X.XX ±0.1mm	APPD		DATE		SIZE: A4			
Δ x					X.XXX ±0.05mm								
MARK	DESCRIPTION				DATE	REVISED	APPROVED						
REVISIONS							UNSPECIFIED TOLERANCES				KXB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											WEIGHT 1.0g		
											SHEET 1/1		
											REVISION A0		