REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	



规格 Specification：

1.额定值 Rating:6A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles

5.操作力 Operation force:350±150gf

6.所有材料符合Rohs要求 All meterials are Rohs compliant





PART NO.:

SS-X 06 26 P G-12 N 1 W W

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS：XKB Vertical handle;
② Enclosure Material:
A—Metal case;
BLANK—Plastic case;
③ Current Rating：06—6A;
④ Switch Circuit:26—2P6T;
⑤ P：Welding plates;
⑥ Handle Shape：G—Camber handle;
⑦ Handle Height：3~15mm;
⑧ Enclosure Shape:N—Square enclosure;
⑨ Terminal specs:
1:TYPE—1；2:TYPE—2；3:TYPE—3;
4:TYPE—4；5:TYPE—5;
⑩ Handle Colour:
B—Black；W—White；R—Red
⑪ Housing Colour:
B—Black；W—White；R—Red







PCB LAYOUT

XKB c US
SS Series
6A 125/250VAC

产品字码标识

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

DESIGN	桑 甚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-0626PG-12N1WW
APPROVED		SIZE: A4	DWG NO.: X-SS-0626PG-12N1WW

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0