




P.C.B LAYOUT



Voltage rating:500V AC/DC

额定电压 :500V AC/DC

Current rating:1.0A

额定电流 : 1.0A

Insulation resistance:1000MΩ Min

绝缘电阻 : 1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压 : ≥500VC/分钟

Temperature range:-40℃-+105℃

使用温度 : -40℃-+105℃

X1270 W R -2x25C - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:W-wafer
- ③ Welding Board Angle:R- Straight 90°
- ④ Row No.-Pin No.:2xXX-2x03P~2x32P
- ⑤ C:With Horns
- ⑥ Material:6T-Nylon PA6T UL94V-0
- ⑦ Planting Category:V01-All Gold Flash

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
2x03	2.54	18.31
2x04	3.81	19.58
2x05	5.08	20.85
2x06	6.35	22.12
2x07	7.62	23.39
2x08	8.89	24.66
2x09	10.16	25.93
2x10	11.42	27.20
2x12	13.97	29.74
2x13	15.24	31.01
2x15	17.78	33.55
2x17	20.32	36.09
2x20	24.13	39.90
2x25	30.48	46.25
2x30	36.83	52.60
2x32	39.37	55.14

X1270WR-2x25C-6TV01	Nylon-6T UL 94V-0	Brass	Gold Flash	X1270H-2x25
				X1270H1-2x25
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: Horn type connector
DWN		VIEW:	PART NO.: X1270WR-2x25C-6TV01
CHKD		UNIT: mm/in	DWG NO.: X-X1270WR-2x25C-6TV01
APPD		SIZE: A4	
		WEIGHT	SHEET
		1/1	REVISION A0