






02P~10P



11P~30P



#### Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance: 500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X9862 H -05 A- N0

① ② ③ ④ ⑤

1.Series No

2.Category:H-HSG

3.Row No.Pin No:XX-02P-30P

4.Special N0:A-With Lock

5.Material:N0-Nylon 66 UL 94V-0

| Poles | Dimensions(mm) |       |       |
|-------|----------------|-------|-------|
|       | A              | B     | C     |
| 02    | 1.25           | 4.40  | 2.75  |
| 03    | 2.50           | 5.65  | 4.00  |
| 04    | 3.75           | 6.90  | 5.25  |
| 05    | 5.00           | 8.15  | 6.50  |
| 06    | 6.25           | 9.40  | 7.75  |
| 07    | 7.50           | 10.65 | 9.00  |
| 08    | 8.75           | 11.90 | 10.25 |
| 09    | 10.00          | 13.15 | 11.50 |
| 10    | 11.25          | 14.40 | 12.75 |
| 11    | 12.50          | 15.65 | 14.00 |
| 12    | 13.75          | 16.90 | 15.25 |
| 13    | 15.00          | 18.15 | 16.50 |
| 14    | 16.25          | 19.40 | 17.75 |
| 15    | 17.50          | 20.65 | 19.00 |
| 20    | 23.75          | 26.90 | 25.25 |
| 25    | 30.00          | 33.15 | 31.50 |
| 30    | 36.25          | 39.40 | 37.75 |

|               |                      |                       |                          |
|---------------|----------------------|-----------------------|--------------------------|
| X9862H-05A-N0 | Nylon 66<br>UL 94V-0 | X9862W-A              | X9862T-A                 |
| PART NO       | Material             | Suitable XKB<br>Wafer | Suitable XKB<br>Terminal |

| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|
| ΔX                                            |             |      |         |          | ANGULAR ±5°            |
| ΔX                                            |             |      |         |          | L≤ 4 ±0.2              |
| ΔX                                            |             |      |         |          | 4<L≤ 16 ±0.3           |
| ΔX                                            |             |      |         |          | 16<L≤ 63 ±0.4          |
| ΔX                                            |             |      |         |          | L> 63 ±0.5             |
| REVISIONS                                     |             |      |         |          |                        |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|                       |  |                                                                                             |                                             |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|---------------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>1.25mm Crimp Style Connector |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X9862H-05A-N0                  |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X9862H-05A-N0                 |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                             |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                      | SHEET | REVISION |
|                       |  |                                                                                             |                                             | 1/1   | A0       |