






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.05.19	阿树
A1	N/A	②X1	/	2025.09.28	阿树



Specifications:

规格:

Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃--+130℃
温度范围: -25--+130℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:30mΩ Max
接触电阻: 30mΩ Max

PART NO.:

X2002 F R S-05-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:F-Female
③Welding Board Angle:R-Stright 90°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-05Pin
⑥Material:LP-LCP UL 94V-0
⑦Plating:SN-Tin Plated

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.0mm BTB Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2002FRS-05-LPSN
APPROVED		SIZE:	A4	DWG NO.:	