





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2024.9.18	阿树
A2	ECN-P-2025091003	②X1	产品尺寸及外观	2025.09.10	阿树



2P Shape






3P Shape

- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:−40°C~+125°C
 - Insulation resistance:≥1000MΩ

PART NO.:

X9556 H-12 B-N0 XX
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~20P
④Special No.:
B-There are convex point and the buckle
⑤Material:N0-PA66 UL94V-0
⑥Color:Blank-Natural Color
HF-Halogen free



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.54	5.08	12	27.94	30.48
03	5.08	7.62	13	30.48	33.02
04	7.62	10.16	14	33.02	35.56
05	10.16	12.70	15	35.56	38.10
06	12.70	15.24	16	38.10	40.64
07	15.24	17.78	17	40.64	43.18
08	17.78	20.32	18	43.18	45.72
09	20.32	22.86	19	45.72	48.26
10	22.86	25.40	20	48.26	50.80
11	25.40	27.94			

X9556H-12B-N0HF	Nylon 66 UL 94V-0 Halogen Free	X9556T	X9556W
X9556H-12B-N0	Nylon 66 UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 2.54mm Crimp Style Connector		
PART NO.: X9556H-12B-N0		
DWG NO.: X-X9556H-12B-N0		
SCALE N/A	PAGE 1/1	REVISION A2