






02P~04P Single Hole  
Scale 1:0.7



## Specifications:

规格:

1.Voltage rating:150VAC/DC

额定电压: 150V AC/DC

2.Current rating:3A AC/DC

额定电流: 3 A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: 500V AC/ 分钟

4.Temperature range: -25 ℃ -+85℃

温度范围: -25℃ -+85℃

5.Insulation resistance:1000MΩ

绝缘电阻: 1000MΩ

6.Contact resistance:20mΩ

接触电阻: 20mΩ

7.After environmental testing:40mΩ

环境测试后: 40 mΩ

X1503 WRS-09 -4TV01  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category:W-Water
- ③ Welding Board Angle:R-Straight 90°
- ④ Welding Way S-SMT
- ⑤ Row No -Pin No:XX-02P-12P
- ⑥ Plug the pin&special No
- ⑦ Material:4T PA4T 94V-0
- ⑧ Planting style:V01-Gold-Flash

| Poles | Dimensions(mm) |       |       |       |
|-------|----------------|-------|-------|-------|
|       | A              | B     | C     | D     |
| 02    | 1.50           | 6.75  | 2.85  |       |
| 03    | 3.00           | 8.25  | 4.35  |       |
| 04    | 4.50           | 9.75  | 5.85  |       |
| 05    | 6.00           | 11.25 | 7.35  | 3.00  |
| 06    | 7.50           | 12.75 | 8.85  | 3.00  |
| 07    | 9.00           | 14.25 | 10.35 | 4.50  |
| 08    | 10.50          | 15.75 | 11.85 | 6.00  |
| 09    | 12.00          | 17.25 | 13.35 | 7.50  |
| 10    | 13.50          | 18.75 | 14.85 | 9.00  |
| 11    | 15.00          | 20.25 | 16.35 | 10.50 |
| 12    | 16.50          | 21.75 | 17.85 | 12.00 |

|                   |              |               |             |                      |                    |                      |
|-------------------|--------------|---------------|-------------|----------------------|--------------------|----------------------|
| X1503WRS-09-4TV01 | PA4T UL94V-0 | Brass         | Gold-Flash  | Brass                | Tin                | X1503H               |
| PART NO           | Material     | Material(Pin) | Finish(Pin) | Material Solder Tabs | Finish Solder Tabs | Suitable XKB Housing |

|                       |  |                                                                                             |                                        |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|----------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>Wire to Board Connector |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X1503WRS-09-4TV01         |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X1503WRS-09-4TV01        |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                        |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                 | SHEET | REVISION |
|                       |  |                                                                                             |                                        | 1/1   | A0       |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                            |             |      |         |          | L ≤ 4                  | ±0.2 |
| Δx                                            |             |      |         |          | 4<L ≤ 16               | ±0.3 |
| Δx                                            |             |      |         |          | 16<L ≤ 63              | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |
|                                               |             |      |         |          |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED