



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2004 W R-04- N0 SN


① ② ③ ④ ⑤ ⑥

- ① Series No.
 ② Category : W-WAFER
 ③ Wedding Board Angle : R-Sright 90°
 ④ Row No.-Pin No.: XX-02P~16P
 ⑤ Material : N0-PA66 94V-0
 ⑥ Plating Category: Sn-Bright Tin Plating




02P~15P Double Gap


Scale 1:1



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	5.96	4.96	10	18.00	21.96	20.96
03	4.00	7.96	6.96	11	20.00	23.96	22.96
04	6.00	9.96	8.96	12	22.00	25.96	24.96
05	8.00	11.96	10.96	13	24.00	27.96	26.96
06	10.0	13.96	12.96	14	26.00	29.96	28.96
07	12.0	15.96	14.96	15	28.00	31.96	30.96
08	14.0	17.96	16.96	16	30.00	33.96	32.96
09	16.0	19.96	18.96				



Recommended P.C.B Layout
 General Tolerance±0.05



02P~03P Single Gap

Scale 1:1

X2004WR-04-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2004H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

△X	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△X					
△X					
△X					
MARK					
REVISIONS					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	2.0mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	PART NO.:
APPD		DATE		SIZE: A4	X2004WR-04-N0SN
XKB INDUSTRIAL PRECISION CO.,LIMITED					DWG NO.:
					X-X2004WR-04-N0SN
WEIGHT		SHEET		REVISION	
1.0g		1/1		A0	