


REVISONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.30	阿树

- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:1000V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ

PART NO.:


X9555 H3-2x04 B-PT V01
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:H3-HSG With TYPE 2
③Row No.Pin No:2xXX-2x03~2x32Pin
④Special:NO:X-Type A;Type B;Type C
Blank-conventional product
⑤Material:PT-PBT 94V-0
⑥Plating:V01-Gold Flash




TYPE 2




X9555H3-2xXX-PTV01	PBT	BRASS	Gold Flash	XPD1.27-A28PXX-IDC	X9555WV-2xXX	X9555HI-2xXXA
					X9555WR-2xXX	X9555HI-2xXXB
					X9555WVS-2xXX	X9555HI-2xXXC
					X9555WV-2xXX	X9555HI-2xXXA
X9555H3-2xXXX-PTV01					X9555WR-2xXX	X9555HI-2xXXB
					X9555WVS-2xXX	X9555HI-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XK B Wafer	Suitable XK B flat cable	Suitable XK B DIP



Y型端子



14P-64P 双槽



6P 小鼻/无槽
TYPE C

6P 大鼻/无槽
TYPE A

8P 大鼻/无槽
TYPE A

6P 小鼻/单槽
TYPE B

8P 小鼻/单槽
TYPE B

10P-12P 单槽
Blank

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
2x03	12.32	5.08	1.9	2x13	37.72	30.48	3.80
2x04	14.86	7.62	小1.9/ 大3.8	2x15	42.80	35.56	
2x05	17.40	10.16	3.8	2x17	47.88	40.64	
2x06	19.94	12.70		2x18	50.42	43.18	
2x07	22.48	15.24		2x20	55.50	48.26	
2x08	25.02	17.78		2x22	60.58	53.34	
2x09	27.56	20.32		2x25	68.20	60.96	
2x10	30.10	22.86		2x30	80.90	73.66	
2x11	32.64	25.40		2x32	85.98	78.74	
2x12	35.18	27.94					

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.54mm IDC
CHECKED		UNIT: mm/in	PART NO.: X9555H3-2x04B-PTV01
APPROVED		SIZE: A4	DWG NO.: X-X9555H3-2x04B-PTV01

SCALE	PAGE	REVISION
N/A	1/1	A1