



NUMBER OF POSITIONS	DIMENSION		
	A	B	C
2x03	2.54	8.00	11.80
2x04	3.81	9.27	13.07
2x05	5.08	10.54	14.34
2x06	6.35	11.81	15.61
2x07	7.62	13.08	16.88
2x08	8.89	14.35	18.15
2x10	11.43	16.89	20.69
2x12	13.97	19.43	23.23
2x13	15.24	20.70	24.50
2x15	17.78	23.24	27.04
2x16	19.05	24.51	28.31
2x17	20.32	25.78	29.58

NUMBER OF POSITIONS	DIMENSION		
	A	B	C
2x18	21.59	27.05	30.85
2x20	24.13	29.59	33.39
2x22	26.67	32.13	35.93
2x25	30.48	35.94	39.74
2x30	36.83	42.29	46.09
2x32	39.37	44.83	48.63
2x33	40.64	46.10	49.90
2x34	41.91	47.37	51.17
2x35	43.18	48.64	52.44
2x37	45.72	51.18	54.98
2x38	46.99	52.45	56.25
2x40	49.53	54.99	58.79

X1270H2-2x03-PTV01	PBT UL 94V-0	Phosphor Bronze	Gold Flash	X1270WV-2x03B1 X1270WVS-2x03B1	XPD0.635-A30PXX-IDC	X1270HI-2x03
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Wafer	Suitable XKB flat cable	Suitable XKB DI

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						



DSND		SCALE: N/A	MODEL TYPE: 1.27mm IDC Connectors		
DWN		VIEW: 	PART NO.: X1270H2-2x03-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X1270H2-2x03-PTV01		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0