







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.19	阿树



Specifications:
1.Voltage rating: 300V AC/ DC
2.Current rating: 1A AC/DC
3.Withstanding voltage: 900V AC/minute
4.Temperature range: -25° ~+85
5.Insulation resistance: 100MΩ Min
6.Contact resistance: 20mΩ Max
7.Material:LCP Black UL94V-0
PIN Brass Tin-plated

PART NO.:
X5400 W F-02-LP SN
① ② ③ ④ ⑤ ⑥
①Series No
②Category:W-Wafer
③Welding Board Angle: F-Female
④Row No.-Pin No.: XX-Single Row
⑤Material: LP-LCP UL94V-0
⑥Plating Category: SN-Tin Plating

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X5400WF-02-LPSN		LCP	Brass	Tin-Plating	X5400WM
PART NO		Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer
DESIGN	阿树	VIEW:	MODEL TYPE: 5.4mm BTB Style Connectors		
CHECKED		UNIT: mm/in	PART NO.: X5400WF-02-LPSN		
APPROVED		SIZE: A4	DWG NO.:		
SCALE				PAGE	REVISION
N/A				1/1	A1