





02~20P




P.C.B LAYOUT


PART NO.:

X9862 W R S-02 A-6T SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W—Wafer
③Welding Board Angle:R—Stright 90°
④Welding Way:S—SMT
⑤Special NO:A—With Lock
⑥Row No.Pin No:XX-02~25Pin
⑦Material : 6T—PA6T 94V-0 Beige
⑧Planting Cateogtry:SN—Bright tin plating




Circuit 1



■ SPECIFICATIONS

- Voltage rating:150V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤30mΩ

Poles	Dimensions(mm)	
	A	B
02	1.25	4.40
03	2.50	5.65
04	3.75	6.90
05	5.00	8.15
06	6.25	9.40
07	7.50	10.65
08	8.75	11.90
09	10.00	13.15
10	11.25	14.40
11	12.50	15.65
12	13.75	16.90
13	15.00	18.15
14	16.25	19.40
15	17.50	20.65
20	23.75	26.90
25	30.00	33.15



21~25P

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XK13 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.25mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X9862WRS-02A-6TSN	
APPROVED		SIZE: A4	DWG NO.: X-X9862WRS-02A-6TSN	
PRECISION CO., LIMITED			SCALE	PAGE
			N/A	1/1
			REVISION	
				A1