








Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 500M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing : $\leq 30m\Omega$

X1502 W V S-03-9T SN

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Material : 9T-PA9T;6T-PA6T;LP-LCP 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	6.00	3.60	09	12.00	16.50	14.10
03	3.00	7.50	5.10	10	13.50	18.00	15.60
04	4.50	9.00	6.60	11	15.00	19.50	17.10
05	6.00	10.50	8.10	12	16.50	21.00	18.60
06	7.50	12.00	9.60	13	18.00	22.50	20.10
07	9.00	13.50	11.10	14	19.50	24.00	21.60
08	10.50	15.00	12.60	15	21.00	25.50	23.10

X1502WVS-03HF-LPSW	LCP UL 94V-0 Halogen Free	Brass	Tin-Plated	X1502T
X1502WVS-03-6TSN	PA6T UL 94V-0			
X1502WVS-03-9TSN	PA9T UL 94V-0			
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

General Tolerance±0.05							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors		
ΔX					ANGULAR	±5°	DWN		DATE		VIEW: 	PART NO.: X1502WVS-03-9TSN		
ΔX					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1502WVS-03-9TSN		
ΔX					4<L ≤ 16	±0.3								
ΔX					16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION					L > 63								
REVISIONS							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
												1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														