






1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2024.08.28	



Specifications:

Voltage rating:50V AC/DC
50V AC/DC
Current rating:1A AC/DC
1A AC/DC
Withstanding voltage:500V AC/minute
500V AC/
Temperature range:-40 ~+125
-40 ~+125
Insulation resistance:100MΩ min
100MΩ Min
Contact resistance:20mΩ Max
20mΩ Max

PART NO.:
X1011 H-2x08-N0 HF

- 1.Series No
2.Category:H-HSG
3.Row No.Pin No:2x04~2x25
4.Material:N0-Nylon66 (White) UL 94V-0
5:HF-Halogen Free

Poles	Dimensions/mm		
	A	B	C
2x04	3.00	5.20	7.00
2x05	4.00	6.20	8.00
2x06	5.00	7.20	9.00
2x08	7.00	9.20	11.00
2x09	8.00	10.20	12.00
2x10	9.00	11.20	13.00
2x12	11.00	13.20	15.00
2x15	14.00	16.20	18.00
2x20	19.00	21.20	23.00
2x25	24.00	26.20	28.00

X1011H-2x08-N0HF	Nylon66	X1011W	X1011T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 0.40mm BTB Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1011H-2x08-N0HF
APPROVED		SIZE: A4	DWG NO.:

1

2

3

4