




1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		pin数表尺寸变更, 图面升级整理图面	2024.08.19	阿树



PCB LAYOUT

■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:2.5-1.0A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-45°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ


PART NO.:

X2006 W V-2x04-4T SN
① ② ③ ④ ⑤ ⑥



- ① Series No
② Category:W-WAFER
③ Welding Board Angle:V-180°
④ Row No-Pin No: 2xXX-04P~20P
⑤ Material:4T-PA4T 94V-0
⑥ Plating Category:SN-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	6.00	12	22.00	26.00
03	4.00	8.00	13	24.00	28.00
04	6.00	10.00	14	26.00	30.00
05	8.00	12.00	15	28.00	32.00
06	10.00	14.00	16	30.00	34.00
07	12.00	16.00	17	32.00	36.00
08	14.00	18.00	18	34.00	38.00
09	16.00	20.00	19	36.00	40.00
10	18.00	22.00	20	38.00	42.00
11	20.00	24.00			


X2006WV-2x04-4TSN	PA4T UL 94V-0	X2006T	X2006H
PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing




8P~14P Without Guideway
16P~40P With Guideway
Scale:1/0.5



8P~10P



12P~18P



20P~40P

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2006WV-2x04-4TSN
APPROVED		SIZE:	A4	DWG NO.:	X-X2006WV-2x04-4TSN
		SCALE	N/A	PAGE	1/1
		REVISION			A1

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4