




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2024.12.27	





Current rating:3A AC/DC
3A AC/DC
Temperature range:-40 -+125
-40 -+125

PART NO.:


K 220251 I-P SN-A

K:XKBTEK-Car Connector
XKB Series No
Category:T-Terminal
Material:P-Phosphor Bronze
Plating:SN-Plating Tin
Special No:A-Class A terminal



K220251T-PSN-A	Phosphor Bronze	AWG#28~24	K220251H
PART NO	Material	Wire Range	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2.2mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: K220251T-PSN-A
APPROVED		SIZE: A4	DWG NO.: