



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树





Specifications:
规格:
Current rating:3A AC/DC
额定电流: 3A AC/DC
Voltage rating:250V AC
额定电压: 250V AC
Withstanding voltage:500V AC/MIN
耐受电压: ≥500V AC/分钟
Temperature range:-55℃~+105℃
温度范围: -55℃~+105℃
Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
Contact resistance:30mΩMAN
接触电阻:≤30mΩ
Material And FINISHED:
材料和成本:
INSULATOR:PBT UL 94V-0
绝缘体: PBT UL 94V-0
SHELL: SPCC-SD Plated Ni / Au / Sn
外壳: 铁合金 镀镍/金/锡
CONTACT MATERIAL:COPPER ALLOY
触点材料: 铜合金

PART NO.:

X03 15 F I Z B 2
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :F-Female
- ④T: Tradutlional
- ⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn
- ⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

NO.OF CONTACT	A	B	C
09	30.80	24.99	16.35
15	39.20	33.30	24.75
25	53.05	47.04	38.35
37	69.40	63.50	54.75



铆合方式	TYPE-1:铆合	TYPE-6:直铆锁	TYPE-3:叉锁	TYPE-2:铆合锁螺丝
图式				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	D-SUB	
CHECKED		UNIT: mm/in		PART NO.:	X0315FT7B2	
APPROVED		SIZE: A4		DWG NO.:	X-X0315FT7B2	
CISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1