




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树

Specifications:
规格:
1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
2.Current rating:1A AC/DC
额定电流: 1A AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
4.Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
6.Contact resistance:20mΩMax
接触电阻: ≥20mΩ
Material:
材料:
7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
8.The iron shell:SPCC Nivkel Plating/Tin Plating
铁壳: SPCC,镀镍/镀锡
B、成品不能有弯针, R角不一致等不良。

PART NO.:
X07 37 W I Z BL 3
① ② ③ ④ ⑤ ⑥ ⑦
①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :W-Male
④T: Tradutional C: Car-pin
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U'
5:15U' 6:30U' 7:AuSn
⑥Color:B-BLACK W-White BL-Blue
⑦3:TYPE-3;

NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.65	E±0.25
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.38
37	69.32	63.50	54.75	49.86	45.72

X07XXWXXX3	XDBLS	XDBLM
PART NO	SCREW	NUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	D-SUB	
CHECKED		UNIT: mm/in		PART NO.:	X0737WT7BL3	
APPROVED		SIZE: A4		DWG NO.:	X-X0737WT7BL3	
CISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1